



प. सं. : ०८१। ८२
च.नं.:

लालीगुराँस नगरपालिका

नगर कार्यपालिकाको कार्यालय



(कोशी प्रदेश, नेपाल)

मिति: २०८१/१२/२०

विषय: दररेट उपलब्ध गराईदिने सम्बन्धि सार्वजनिक सूचना

प्रस्तुत विषयमा आ.व. ०८१/०८२ मा यस लालीगुराँस नगरपालिका, तेहथुममा सञ्चालित अपाङ्गता रोकथाम तथा पूनःस्थापना कार्यक्रमको लागी सहायक सामग्रीहरु खरिद गर्ने प्रयोजनको लागी सम्बन्धित आपूर्तिकर्ताले यो सूचना प्रकाशन भएको मितिले ७ (सात) दिन २०८१/१२/२६ गतेभित्र तोकीएको स्पेशिफिकेशन बमोजिमको सामग्रीहरुको तपशिल बमोजिमको ढाँचामा (फर्मको कागजातहरूसहित) कार्यालयमा सोझै वा नगरपालिकाको ईमेल store.laliguransmun@gmail.com मा दररेट उपलब्ध गराईदिनुहुन अनुरोध गर्दछु । तपशिल:


सि. न.	सामग्रीको नाम	स्पेशिफिकेशन	इकाई	परिमाण	प्रतिइकाई मूल्य (भ्याट बाहेक)	भ्याट रकम (१३%) (भ्याट नलाग्ने सामग्री भए खुलाउने)	प्रतिइकाई मूल्य (भ्याट सहित)
१	Walking sticks/canes ISO Code: 12.03.03	<ul style="list-style-type: none">Constructed from mild steel aluminum alloy tubes.ABS handle with comfortable grip.Height-adjustment mechanism: Telescopic, quick-releaseSoft gel on handle topTips securely fitted, non-slip, and replaceable or interchangeableWeight bearing capacity: 110kgSize:Medium	गोटा	१			
२	Walking Frames / Walker ISO Code: 12.06.03	<ul style="list-style-type: none">Rigid steel frameFoldable with net height of 10 cmFoam hand grips for extra comfort.Width/ folded depth: 52cm/10cmHeight: From 79 to 91.5 cmWeight bearing capacity: 3.3kg/125kgSize: Medium	गोटा	१			
३	Manual Wheelchairs ISO Code: 12.22.03	Active wheelchair <ul style="list-style-type: none">Wheelchair with folding or rigid frame, three or four wheels with large rear wheels, seat and backrest, armrests and footrestsFrame: frame with mechanism(s) to fold or dismantle	गोटा	१			



प. सं. : ०८१। ८२
च.नं.:

लालीगुराँस नगरपालिका

नगर कार्यपालिकाको कार्यालय



(कोशी प्रदेश, नेपाल)

	<p>Types:</p> <ul style="list-style-type: none">• Active	<ul style="list-style-type: none">• Backrest or back posts with adjustable height or supplied with a range of back posts with fixed height.• Footrests: with adjustable height to accommodate people with shorter and longer legs. Two flip-up, swing-away or removable footrests on folding frame• Rear wheels: quick-release or removable without tools• Puncture-proof or pneumatic rear tyres and front castors					
४	<p>Wheelchair with postural support (CP wheelchair)</p>	<ul style="list-style-type: none">• CP Chair (with adjustable incline & tray) Hardwood & ply board constructed, naturally finished Chair reclines through an arc and can be adjusted to any desired position.• Comes with adjustable foam padded headrest which can be formed & reformed as needed.• High back supports & holds the child with wide belt.• Laminated activity Tray size 56cm x 63cm with polished wooden raised edges, holds the items from falling.• Adjustable Seat & Foot board are 30cm wide and suits the small children. Mounted on ball bearing castors.• Knee separator	गोटा	१			
५	<p>Semi-Digital and Digital hearing aids with program and volume control ISO Code: 22.06.15</p>	<p>Amplification frequency response and maximum output (OSPL) that meets requirements of standard prescription formulae (e.g. Desired Sensation Level v.5 or National Acoustics Laboratories NL2) Frequency range- 200 to 4500 Hz Adjustable frequency Digital Hearing aids with programs, memory, noise cancellation and volume control etc. 1. Suitable for any severity of hearing loss from moderate (40 dB) to profound (90 dB) degree.</p>	जोर	१			
६	<p>Toilet Chair/ Commode chairs</p>	<ul style="list-style-type: none">• Foldable• Fixed or removable backrest Seat with aperture Removeable collection bucket (pan)• User capacity 100 kg	गोटा	१			



प. सं. : ०८१। ८२
च.नं.:

लालीगुराँस नगरपालिका

नगर कार्यपालिकाको कार्यालय

बसन्तपुर, तेह्रथुम



(कोशी प्रदेश, नेपाल)

	ISO Code: 09.12.03	<ul style="list-style-type: none">• Height adjustable														
७	Pressure Relief mattress ISO Code : 04 33 06	<ul style="list-style-type: none">• Composed of 2.5"-high bubble cells overlay mattresses and easy to install.• Simple to operate , portable and light-weight, this mattress useful for pressure ulcer prevention and treatment.• On/Off switch & rotary dial for pressure setting.• Comfortable, Perfect finish, Robust design, <table border="1"><tr><td>Air output:</td><td>6 - 7 liter/min.</td></tr><tr><td>Pressure:</td><td>40- 100 mmHg</td></tr><tr><td>Cycle time:</td><td>5 to 6 min.</td></tr><tr><td>Size:</td><td>26.5cm (L) x 11cm (W)x 12.5cm (H)</td></tr><tr><td>Weight:</td><td>1.5 kg</td></tr></table>	Air output:	6 - 7 liter/min.	Pressure:	40- 100 mmHg	Cycle time:	5 to 6 min.	Size:	26.5cm (L) x 11cm (W)x 12.5cm (H)	Weight:	1.5 kg	गोटा	१		
Air output:	6 - 7 liter/min.															
Pressure:	40- 100 mmHg															
Cycle time:	5 to 6 min.															
Size:	26.5cm (L) x 11cm (W)x 12.5cm (H)															
Weight:	1.5 kg															
८	Blanket	<ul style="list-style-type: none">• Material: acrylic polyfibre• Soft, cosy and lightweight; ideal for all seasons and weather conditions• 120 GSM thick with hollow siliconized polyester filling• 100% microfibre shell offers a rich, luxurious feel• Hypoallergenic filling helps protect against allergens• Machine stitched pattern is durable keeping filling secure• Dimensions: 225cm x 200cm (90x80)inches• Weight : 3-4 kg	गोटा	१												

पुनः स्वीकृत आपूर्तिकर्ताले स्पेशलफिकेशन बमोजिमको सामग्री नल्याएमा सम्बन्धित आपूर्तिकर्ताको सामग्री फिर्ता गरी नियमानुसार कारवाही समेत गरिने व्यहोरा जानकारीको लागि अनुरोध छ ।

सन्तोष घिमिरे
प्रमुख प्रशासकीय अधिकृत